



4-Speed Wall Control with Receiver - sw405

- Four fan speeds
- Full range light dimmer with incandescent bulbs (250 Watt max)
- Canopy mount receiver included (Not for use on sloped ceilings)
- Operates from up to 30 ft.
- 1.0 amp fan load
- White, light almond and ivory switch cover plates included
- Non-reversing
- One-year limited warranty
- (Wall control only: SW406)

go **ABOVE**[™]

Specifications subject to change without notice.