



## 4-Speed Remote Control with Receiver - SR400

- Four fan speeds
- Full range light dimmer with incandescent bulbs (250 Watt max)
- Canopy mount receiver included (Not for use on sloped ceilings)
- Operates from up to 30 ft.
- 1.0 amp fan load
- Non-reversing
- One-year limited warranty
- Two AAA batteries included
- (Remote only: SR401)

go **ABOVE**<sup>™</sup>

Specifications subject to change without notice.