



LK GLO 
 SERIES
 L.E.D. Light Fixtures

Harnessing the technology of light-emitting diodes, Emerson has created its most energy efficient and longest-lasting light fixtures yet. Our state-of-the-art LK GLO Series Light Fixtures offer our customers increased flexibility in lighting their homes and come in 13 custom finishes. Better still, LK GLO fixtures produce a softer, more uniform glow than conventional bulbs and last nearly three times as long.



LK70LEDXXX
 AMBER MIST
 (4.5" H x 12.38" W)
 One 16 Watt L.E.D. array
 Light Output: 1,200 Lumens
 Color Temperature: 2,700 K
 Color Rendering Index: > 80



LK71LEDXXX
 AMBER PARCHMENT
 (4.5" H X 12.38" W)
 One 16 Watt L.E.D. array
 Light Output: 1,200 Lumens
 Color Temperature: 2,700 K
 Color Rendering Index: > 80



LK72LEDXXX
 AMBER SCAVO
 (4.5" H X 12.38" W)
 One 16 Watt L.E.D. array
 Light Output: 1,200 Lumens
 Color Temperature: 2,700 K
 Color Rendering Index: > 80



LK74LEDXXX
 OPAL MATTE
 (4.5" H X 12.38" W)
 One 16 Watt L.E.D. array
 Light Output: 1,200 Lumens
 Color Temperature: 2,700 K
 Color Rendering Index: > 80



LK77LEDXXX
 WHITE LINEN
 (4.5" H X 12.38" W)
 One 16 Watt L.E.D. array
 Light Output: 1,200 Lumens
 Color Temperature: 2,700 K
 Color Rendering Index: > 80



LK80LEDXXX
 AMBER MIST
 (4.25" H X 12.38" W)
 One 16 Watt L.E.D. array
 Light Output: 1,200 Lumens
 Color Temperature: 2,700 K
 Color Rendering Index: > 80



LK81LEDXXX
 OPAL MATTE
 (4.25" H X 12.38" W)
 One 16 Watt L.E.D. array
 Light Output: 1,200 Lumens
 Color Temperature: 2,700 K
 Color Rendering Index: > 80



LK83LEDXXX
 WHITE LINEN
 (4.25" H X 12.38" W)
 One 16 Watt L.E.D. array
 Light Output: 1,200 Lumens
 Color Temperature: 2,700 K
 Color Rendering Index: > 80



LK141LEDXXX
 GRANDE LIGHT FIXTURE
 WHITE MIST
 (4.25" H X 12.5" W)
 One 16 Watt L.E.D. array
 Light Output: 1,200 Lumens
 Color Temperature: 2,700 K
 Color Rendering Index: > 80



All light fixture bowl caps shown with ORB finish. To complete the model number, replace xxx with finish code. Bowl caps available in AB, AP, AW, BS, DBZ, GBZ, GES, ORB, SW, VNB, VS and WW finishes. Finial packs: Include 3 versions of plates for various pull chain configurations, no hole, 1 hole & 2 hole options included in each pack.

go **ABOVE**™