



## Camden™ - CF3600

**CF3600AP** - Antique Pewter Housing


**CF3600ORH** - Oil Rubbed Bronze Housing with Highlights

- 52" or 44" blade span
- Light fixture adaptable
- 6" downrod included
- K55XL Motor
- Damp Location
- Ships to Canada
- Blades Sold Separately



### Camden™ Select Energy Ratings at High Speed

Airflow Cubic Ft Per Min.	Electricity Use Watts (Excl. Lights)	Airflow Efficiency Cubic Ft Per Min. Per Watt
5658	90	63



A: 15.0" B: 17.0" C: 6.5" D: 6.5"

go **ABOVE**™