



**ADD THE OPTIONAL
WET LOCATION PLATE
FOR OUTDOOR USE:**

For use with LK7X, LK8X series and TB735AMM light fixtures. Shown in ORB. Also available in: AW, DBZ, GES, VS, SW & WW.



**LK70XXX
AMBER MIST**

(4.5" H x 12.38"W)

Three 13-watt medium base compact fluorescent bulbs included.
Rated for three 60-watt incandescent.



**LK71XXX
AMBER PARCHMENT**

(4.5" H x 12.38"W)

Three 13-watt medium base compact fluorescent bulbs included.
Rated for three 60-watt incandescent.



**LK72XXX
AMBER SCAVO**

(4.5" H x 12.38"W)

Three 13-watt medium base compact fluorescent bulbs included.
Rated for three 60-watt incandescent.



**LK74XXX
OPAL MATTE**

(4.5" H x 12.38"W)

Three 13-watt medium base compact fluorescent bulbs included.
Rated for three 60-watt incandescent.



**LK77XXX
WHITE LINEN**

(4.5" H x 12.38"W)

Three 13-watt medium base compact fluorescent bulbs included.
Rated for three 60-watt incandescent.



**LK80XXX
AMBER MIST**

(4.25" H x 12.38"W)

Three 13-watt medium base compact fluorescent bulbs included.
Rated for three 60-watt incandescent.



**LK81XXX
OPAL MATTE**

(4.25" H x 12.38"W)

Three 13-watt medium base compact fluorescent bulbs included.
Rated for three 60-watt incandescent.



**LK83XXX
WHITE LINEN**

(4.25" H x 12.38"W)

Three 13-watt medium base compact fluorescent bulbs included.
Rated for three 60-watt incandescent.



Complete model number by replacing xxx with the final finish code: available in AB, AP, AW, BS, CK, DBZ, GBZ, GES, ORB, VNB and WW finishes. Final packs include 3 installment options: No hole, 1 hole & 2 hole options.

* To use in wet locations, optional wet location plate (WLP100xxx) must be used.

go **ABOVE**[™]